



Aquatac[™] **Primer**

Emulsion Primer for Self-Adhesive Membranes

Physical Properties

-Colour Agua -Solids by Volume 53% (approx.) 1.0 kg/l (approx.) -Weight -Application Temperature

Minus 4°C to 40°C

6 to 12 m²/litre depending on porosity and texture of surface. -Drying Time

Initial Set Set Through -Service Temperature

-Flammability

Wet Dry

@ 50% R.H. 20°C Dry Substrate 30 minutes 2 hours

Minus 40°C to 70°C

Non-Flammable Burns

Description

-Coverage

Aquatac[™] is a polymer emulsion based primer for self-adhesive membranes.

Features

- Quick drying
- Environmentally friendly Low VOC content
- Highly tacky film provides positive adhesion to membrane
- Non-flammable during application
- Easily applied by spray
- Water based, no solvent odours
- Specially designed to provide a high level of tack on vertical surfaces

Uses

Used as primer for self-adhesive membranes such as Blueskin® Breather, DuraTac flashing applications, Blueskin® SA and Blueskin® WP 200 when applied to wood, preserved wood, gypsum board including DensGlass Gold®, polystyrene, masonry, concrete and metal.

Aquatac[™] is the primer of choice when it is necessary to achieve a fast drying, solvent free, tacky surface where walking over the surface is not required during application. This is important for the application of membranes on vertical surfaces. Designed for applications above -4°C.

Limitations

Apply under dry conditions above -4°C. Avoid Freezing, store **Aquatac**[™] above 0°C. If frozen, allow to thaw at room temperature and mix prior to use.

Preparation

Surfaces must be dry and free from dust, dirt, grease, oil or other foreign matter.

Application

Apply by roller at the rate shown. Airless, air assist, or air spray equipment may also be used. Not suitable for use with a garden type sprayer. Pour primer from container into sprayer and spray fine mist over entire substrate. Allow primer to dry thoroughly before applying membrane. Primed surfaces not covered by membrane during the same working day must be reprimed. Aquatac[™] is intended to be used as supplied and need not be diluted.

Clean Up
For uncured film use water. Use mineral spirits for cured films.
Caution
Harmful if swallowed.

Aquatac™ Primer Emulsion Primer for Self-Adhesive Membranes